


DÜRKOPP ADLER AG

DLER AG Phone +49 (0) 521 - 925

Potsdamer Straße 190 E-mail info@duerkopp-

erkopp-adler.com

adjustment with mat








Depending on the material all four corner knife cuts can be set and stored individually, for the main seam and the seam end. Knife corrections are now possible with different

pocket slants and different materials in

all directions.









Programmable, stepper motor-controlled laser marking



The position of the laser marking can be corrected individually in the program and can thus be adjusted to different material thicknesses via fine adjustment. The individual mechanical adjustment of the laser marking during model changes is no longer necessary.









The positions of the transport clamps to the folder sole can be set individually and depending on the material in the program. This allows the automatic conversion from double to single piping and program storage to a wide range of material thicknesses.

Furthermore, it is possible to spread the material after lowering the transport clamp in order to achieve a better seam quality and more precise corner cuts.

